MADEIRA Technical Datasheet

FROSTED MATT No.40

| Article Description | Machine Embroidery T | hread | |
|---|--------------------------|------------------------------|-------------------------------|
| Composition | 96% PES / 4% Ceramic | | |
| Count | 90 dtex x 2 / 80 den x 2 | | |
| Make Up Available | 2500m cone / 1000m spool | | |
| Recommended needle size | 60/8 – 75/11 | | |
| Fastness Rating – Scale 1 (worst) – 5 (best) | | | |
| Fastness to washing at 60°C | | DIN EN ISO 105-C03/M & S C4A | 4-5 |
| Fastness to water (damp for 4hrs at 37°C) | | DIN EN ISO 105-E01/M & S C6 | 4-5 |
| Fastness to rubbing dry (10 rubs on dry white Fabric) DIN EN ISO 105-X12/M & S C8 | | | 4 |
| Fastness to rubbing wet (10 rubs on wet white Fabric) DIN EN ISO 105-X12/M & S | | | 3-4 |
| Fastness to dry cleaning | | DIN EN ISO 105-D01 | 4-5 |
| Fastness to bleaching with Hypochlorite | | DIN EN ISO 105-N01 | 4-5 |
| Fastness to saliva and perspiration according to § 35 LMBG | | | fast |
| Fastness Rating – Scale 1 (worst) – 8 (best) | | | |
| Fastness to light (100hrs xenon light) | | DIN EN ISO 105-B02 | 6-8 |
| | | | (fluorescent colors excluded) |
| Mechanical – Technological Values | | | |
| Tensile Strength cN (force until thread breaks, in Centinewton) | | DIN EN ISO 2062 | ca.650cN |
| Elongation (% of stretch extension with weight tension until breaks) | | | ca.28 |
| Shrinkage (shrinkage at boiling water) | | DIN 53866 T2 | < 1% |

Recommendations for care



max. 20g/l active chlorine- max. 30°C - max. 30 min

Color Card No.

Öko-Tex



To improve this product Madeira reserves the right to alter the specifications or modify the appearance of products without notice. Information and technical data in this document are guidelines and no warranted characteristics. Small variations due to production process are possible.

MADEIRA Garnfabrik Rudolf Schmidt KG Zinkmattenstraße 38 D-79108 Freiburg Tel.: +49 (0) 761 – 51 04 00 E-Mail: service@madeira.de



111